# Linishing machine GI, Type: 790202

## Order data

| | |
|---|---|
| Order number | 077613 790202 |
| GTIN | 2050001676764 |
| Item class | 03H |

## Description

**Version:**
GRIT GI linisher range for demanding industrial applications: **Sturdy design**, with **extremely power motors**.
- **High efficiency due to best removal rate.**
- **Powerful 4 kW motor (400 V, 3 ~, 50 Hz).**
- **Patented belt-tensioning system,**
- **High operational safety: Stop, linishing gap, and eye protection are individually adjustable.**

The **basic module** for industrial belt linishing.
- **Easy to use, low-vibration running.**
- **With constant speed for high metal removal rates.**
- **Can be connected to a central vacuum system.**

**Application:**
As a **linishing machine**, **when mounted on machine mount** No. 077614, **with extension modules for radial, longitudinal, surface, and centreless grinding and deburring.**
**Supplied with:**
CEE plug (16 A), 1 linishing belt.
**Note:**
For linishing belts see No. 558310 ff and No. 558453-56.

## Technical description

| | |
|---|---|
| maximum speed 2nd speed | 3000 $min^{-1}$ |

| | |
|---|---|
| Manufacturer's designation | GI 75 2H |
| maximum speed 1st speed | 1500 $min^{-1}$ |
| Tape width | 75 mm |
| Weight | 65 kg |
| Band length | 2000 mm |
| Power supply | Mains operated |
| Overall width | 540 mm |
| Overall length | 970 mm |
| Overall height | 1020 mm |
| Type of product | Linishing machine |

## Accessories

| | |
|---|---|
| Machine mount Type 99001003 | 077614 99001003 |
| Machine mount Type 99001004 | 077614 99001004 |
| Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 120 | 558310 120 |
| Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 40 | 558310 40 |
| Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 60 | 558310 60 |
| Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 80 | 558310 80 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120 | 558453 120 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36 | 558453 36 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60 | 558453 60 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80 | 558453 80 |

| | |
|---|---|
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120 | 558454 120 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36 | 558454 36 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60 | 558454 60 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80 | 558454 80 |
| Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36 | 558456 36 |