Be sure. testo

Air and infrared temperature measuring device, Type: 810

Order data

Order number	474260 810
GTIN	4029547008320
Item class	47B

Description

Version:
Handy device, easy to operate, high quality sensors with long-term stability. Hold function, min / max memory and display illumination for ease of reading the measurement values.
Supplied with:
Supplied with test certificate, protective cap, belt bag and 2 batteries No. 081561 size LR3.

Technical description

Error limit infra-red	±2 °C
Optics	6: 1
Length	119 mm
Width	46 mm
Measuring range infra-red	-30 - 300 °C
Height	25 mm
Error limit air	±0.5 °C

Measuring range air	-10 - 50 °C
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Calibration	I5
Calibration	I9
Type of product	Temperature measuring device

Services

DAkkS calibrationThermo-hygrometer Type A	027670 A
DAkkS calibrationInfra-red temperature measuring tool Type A	027610 A
CalibrationTemperature measuring device, room temperature Type B	027650 B
CalibrationInfra-red temperature measuring tool Type A	027600 A

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3