Garant

Try square stainless, accuracy class 1, Stock length: 300X200mm

Order data

Order number	451040 300X200
GTIN	4045197444226
Item class	41G

Description

Version:
All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Protective packaging for safe transport.
Application:
For inspection and high precision work.
Accuracy:
DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Technical description

Shank cross-section	40×8 mm
Right angle tolerance	0.025 mm
Stock length	300×200 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

Accessories

Wooden case for stock length 300X200 mm	451600 300X200