Mitutoyo

Micrometer head, Measuring range (travel): 0-25/Fmm

Order data

Order number	426200 0-25/F
GTIN	4946368023151
Item class	44A

Description

Version:
Fully hardened spindle and glare-free satin chrome-plated barrel. **Stationary (non-rotating)** spindle with carbide tipped contact face and ratchet. For checking materials with delicate surfaces.
Application:
For installation in machines, inspection fixtures, measuring instruments etc. as an adjustable comparator stand stop.
Note:
Special sizes on request.

Technical description

Spindle ∅	8 mm
Mounting shank ∅	12 mm
Barrel ∅	18 mm
Overall length	125 mm
Length of mounting shank	10 mm
Scale divisions	0.01 mm
Error limit	0.003 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Calibration	B3
Type of product	Micrometer head

Services

CalibrationMicrometer head maximum measuring range 25 mm	022280 25
DAkkS calibrationMicrometer head maximum measuring range 50 mm	022290 50