Clamp toolholder, left-hand, Shank / insert size: 32/16mm

Order data

Order number	250007 32/16
GTIN	4045197861634
Item class	21T

Technical description

suitable indexable insert	CN.. 1606..
ISO code toolholder	MCLNR/L 3232P16
Screw for clamping claw	259021 1
Shim	259031 23
Shim screw	259025 7
Insert size	16 mm
Clamping claw	259038 4
Shank size	32 mm
Head length L_1	34 mm
Functional width L_4	40 mm
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 23	259031 23
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 7	259025 7
Clamping claw Type 4	259038 4
Screw for clamping claw Type 1	259021 1
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500