# Threads “No Go” ring gauge 6g, Thread: M3

## Order data

| | |
|---|---|
| Order number | 486050 M3 |
| GTIN | 2050001037275 |
| Item class | 48B |

## Description

**Version:**
The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.
**Application:**
For metric ISO threads, right-hand DIN 13.
**Standard:**
Toleranzen und Abmaße nach **DIN ISO 1502.**
**Note:**
Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

## Technical description

| | |
|---|---|
| Thread pitch | 0.5 mm |
| Tolerance class | 6g |
| Thread | M3 |
| Calibration | L12 |

| | |
|---|---|
| Tolerance zone | g |
| Type of gauge | “No Go” gauge |
| Standard | DIN 13 |
| Thread type | M |
| Quality | 6 |
| Type of product | Thread “No Go” ring gauge |

## Services

| | |
|---|---|
| CalibrationThread ring gauge maximum ∅ 3 mm | 028600 3 |
| DAkkS calibrationThread “Go” ring gauge maximum ∅ 100 mm | 028640 100 |