VSM

# Abrasive cloth (A) economy roll, brown KK 114 F, 40 mm × 50 m, Grit: 180

## Order data

| | |
|---|---|
| Order number | 557700 180 |
| GTIN | 4018875266649 |
| Item class | 56V |

## Description

**Version:**
Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A).**
Very good grit bonding, high abrasion performance and long service life.
Type **VSM KK 114 F: Brown fabric, for extremely demanding applications.** This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying.
Packaging tape **with integral tear-off cutter.**
**Application:**
Predominantly for rubbing down metals by hand, but also suitable for all other materials.

## Technical description

| | |
|---|---|
| Grit designation | fine |
| Grit | 180 |
| Series | KK114F |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |

| | |
|---|---|
| Economy roll width | 40 mm |
| Economy roll length | 50 m |
| Product name attribute | 40 mm × 50 m |
| Type of product | Abrasive cloth |

## User data

| | Suitability | $V_c$ | ISO code |
|---|---|---|---|
| Alu Mg | suitable | | |
| Steel < 900 N/mm² | suitable | | |
| Steel < 1400 N/mm² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |