PFERD

Milled tooth file 350×36×4.7 mm, Tooth type: 2

Order data

Order number	519200 2
GTIN	4007220016244
Item class	53B

Description

Version:
Teeth on both sides, milled radially from the solid; top side **convex** – this **prevents scratches** on the component from the edges of the file. The special tooth shape and the positive cutting angle ensure high filing performance.
Cuts convex on both faces.
Application:
Suitable for working sheet metal, particularly in **car production**, **bodywork building** and **car body repairs. Using these milled tooth files, groove-free, smooth surface finishes are obtained which can be painted without polishing.**

Technical description

Tooth type	2
Tooth spacing approx.	2.5 mm
Grit designation	medium
Cross section	36×4.7 mm
Overall length	350 mm
Type of product	Milled tooth file

Accessories

File brush Bristle length L3× width L1 100X25 mm	576000 100X25

File brush Bristle length L3× width L1 115X40 mm	576000 115X40
File brush Bristle length L3× width L1 80X20 mm	576000 80X20
Adjustable blade holder for milled tooth file 350 mm Type KFH350	519215 KFH350