HOLEX

Turning tool right-hand, similar to DIN 4972 (ISO 2), M20, Shank square: 25mm

Order data

Order number	296130 25
GTIN	4045197884756
Item class	22E

Description

Version:
Fitted with diamond ground carbide inserts.
Application:
P20/K25 for machining steel and cast iron.
M20 for machining stainless steels.
Attention:
For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank square	25 mm
Overall length	140 mm
Tool material	M20
Type of product	Turning tool