uvex

Lace-up boot, black/yellow uvex 1, S2, EU shoe size: 36

Order data

Order number	092118 36
GTIN	4031101534787
Item class	04V

Description

Version:
Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.
- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Lace-up boot with soft padded collar and padded tongue.
Standard:
EN ISO 20345:2011 S2 SRC
Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Technical description

Material of outer sole	Polyurethane
against water penetration and water absorption	yes
Energy absorption in the heel area	yes

The entire shoe is waterproof	yes
Shoe type	Lace-up boots
Protection class	S2
Colour	black / yellow
Standard	Inlay type-tested according to DGUV regulation 191
oil- and petrol-resistant sole	yes
Material inner lining	Distance Mesh
contains no metal or leather	yes
anti-static	yes
suitable for those with chrome allergy.	yes
removable footbed	yes
Material of protective toe-cap	Composite
Uppers material	Hydrophobic high-tech micro-velour
EU shoe size	36
Slip resistance	yes
Closure	laces
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots