Carbide-tipped multi-purpose drill set long, ∅: 6-12mm



Order data

Order number	787055 6-12
GTIN	9002741072880
Item class	76G

Description

Version:
The carbide insert is diamond ground all round, giving **extra-sharp, super-hard cutting edges.**
Patented 4-step profile for quick removal of chips and swarf.
Overall length 400 mm, flute length 300 mm.
Application:
Precise **drilling** in tiles, masonry and concrete, metal, wood, and plastics.
Content:
1 each drill: Size (∅) 6; 8; 10; 12 mm
Note:
Caution - only for rotary use (without hammer action!)

Technical description

Number of drills	4
Drill ∅	6 - 12 mm
Number of cutting edges Z	2
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

Accessories

Carbide-tipped multi-purpose drilllong ∅ 10 mm	787045 10
Carbide-tipped multi-purpose drilllong ∅ 12 mm	787045 12
Carbide-tipped multi-purpose drilllong ∅ 6 mm	787045 6
Carbide-tipped multi-purpose drilllong ∅ 8 mm	787045 8