Fine stoneware drill /tiles drill, Ø: 8mm

Order data

Order number	787035 8
GTIN	9002741151363
Item class	76G

Description

Version:
2 pieces. A drill with a **diamond-ground carbide tip** with a patented centring tip for highly accurate start positioning and exact holes without break-outs. With 10 mm shank. A carbide drill for use in standard drill chucks. With 1/4 inch (E 6.3) hexagon shank.
Application:
For **very hard stoneware tiles** up to Mohs / scratch hardness class 9 and for glass and porcelain.
Note:
Not suitable for hammer drills. Maximum spindle speed 200 rpm. No cooling required.

Technical description

Use with impact / without impact	not for impact drilling
Tool material	Carbide
Number of drills	2
Shank	Plain shank
maximum speed	200 min^{-1}

Shank ∅	10
Bit hexagon shank	E 6,3
Overall length	120 mm
∅	8 mm
Type of product	Masonry drill