KNIPEX

Side cutter polished, overall length: 160mm



Order data

Order number	724900 160
GTIN	4003773213420
Item class	73F

Description

Version:
Slim shape with induction hardened cutting edges (approx. 62 HRC).
Jaws chemically blacked, polished head, plastic coated handles.
Standard:
DIN ISO 5749
Material:
Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to ∅	4 mm
overall length	160 mm
Cutting capacity hard wire up to ∅	2 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no

with selectable return spring	no
Type of product	Cutting pliers