Heavy-duty combi pliers, chrome-plated, with grips, overall length: 225mm

Order data

Order number	700400 225
GTIN	4003773010005
Item class	73F

Description

Version:
Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire.
Jaws chrome-plated, handles with multi-component covering.
Standard:
DIN ISO 5746.
Material:
Special tool steel, drop-forged, and oil-hardened.

Technical description

overall length	225 mm
Cutting capacity hard wire up to ∅	3 mm
Cutting capacity piano wire up to ∅	2.5 mm
Standard	DIN ISO 5746
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel
Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers