Garant

Toolholder for metric profile broaching tools ∅ d = 8 mm, Shank ∅ DS: 20mm

Order data

Order number	293020 20
GTIN	4045197945907
Item class	29K

Description

Suitable for:
CNC and conventional machines.
Optional extras:
Positioning aid (No. 293000) and pin wrench (No. 293006).
Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MT2, MT3 and MT4.
Note:
- **Caution: Always use appropriate slotting tool ∅.**
- **Other shank connections on request.**

Technical description

L	38 mm
Shank length L_s	50 mm
Shank type	Plain shank
Shank ∅ D_S	20 mm
∅ D	33 mm

∅ d	8 mm
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

Accessories

Pin spanner for holder ∅ 16 mm	293006 16
Pin spanner for holder ∅ 12 mm	293006 12
Pin spanner for holder ∅ 8 mm	293006 8
Pin spanner for holder ∅ 5 mm	293006 5