Hoffmann Group

Screw-on toolholder, neutral, Shank / insert size: 8/07mm

Order data

Order number	261317 8/07
GTIN	4045197948403
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Insert size	7 mm
Pack of insert screws	269028 27
Shank size	8 mm
Overall length L neutral holders	125 mm
ISO code toolholder	SVVCN 0808K07
Functional width L_4 neutral holders	4 mm
Overhang L_1 neutral holders	15 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriverwith scale, to take interchangeable blades maximum torque 200 cNm	659957 200