Garant

Four-way ratchet ring spanner “4 in 1”, Type: 16-19

Order data

Order number	614847 16-19
GTIN	4045197972903
Item class	61B

Description

Version:
With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats.
Extremely small working arc of 5°.
Material:
Chrome vanadium steel, matt chrome-plated.

Technical description

Width across flats	metric
Width across flats 1	16 mm
Width across flats 4	19 mm
maximum ring height h_2	21.9 mm
maximum ring ∅ D2	33.5 mm
Width across flats 2	17 mm
overall length L	230 mm
maximum ring height h_1	20.2 mm
Width across flats 3	18 mm
maximum ring ∅ D1	31.5 mm
No. of teeth	72
Working arc	5 degrees

Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner