Safety helmet G3000, Colour: YELLOW

Order data

Order number	097815 YELLOW
GTIN	4046719316724
Item class	04M

Description

Version:
Safety helmet of UV-stabilised ABS. The **integral UV sensor** indicates when the helmet has become brittle due to high exposure to UV and should be replaced. The internal arrangement can be turned through 180 degrees and allows wearing of a screen at the neck (an advantage when working in restricted spaces). **Good ventilation** of the upper shell of the helmet. **Resistant to low temperatures down to -30 °C** and protection against splashes of liquid metal (MM).
· **4-point strap attachment, height adjustable**
· **30 mm Euro slot mounting**
· **Plastic sweatband**
· **Straight form**
· **With rotary catch**
Application:
Industry, building trade, forestry.
Standard:
DIN EN 397
Specification:
Resistant to low temperatures down to -30° C and protection against splashes of liquid metal (MM)
Suitable for:
Ear defenders No. 097753; 097756
Spare part:
No. 097825 standard sweat band. No. 097826 leather sweat band.

Technical description

Can be turned 180°	yes
Weight	310 g
free of internal and external condensation	yes
Resistance to weld spatter (MM)	yes
UV-sensor for exchange notification	yes
Resistance to cold	up to -30 °C
Width adjustment	Silicone-free
Colour	yellow
Size	53 - 62 cm
Helmet characteristics	Safety characteristics down to -30 °C
Helmet characteristics	Protection against liquid metal spraying out
Material of helmet shell	ABS
Standard	DIN EN 397
Type of product	Safety helmet

Accessories

Ear defendersPeltor™ Optime™ helmet series Type 1	097753 1
Ear defendersPeltor™ Optime™ helmet series Type 2	097753 2
Ear defendersPeltor™ Optime™ helmet series Type 3	097753 3
Ear defenders Type HELMET	097795 HELMET
Standard sweatbandHYG3	097825
Leather sweatbandHYG4	097826
Helmet adapterP3EV	097827
Safety glasses with helmet attachmentV9C	097829
Chinstrap GH4 Suspension 3P	097833 3P

Attachment for clear visorPeltor™ G500 Manufacturer's designation G500-GU	097872 G500-GU