Carbide core drill Depth of cut 35 mm, Ø DC: 16mm

Order data

Order number	119000 16
GTIN	4014586240039
Item class	03G

Description

Version:
High-performance carbide core drill with QuickIN holder. For maximum tool life and excellent metal removal rate.
Overall length: 77 mm for all cutter sizes.
Suitable for:
FEIN core drilling machines with QuickIN holder for fast, keyless tool changes. Also suitable for other makes with adapter. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.
Supplied with:
Without centring pin.
Note:
For FEIN core drilling machines see No. 076520/ 076524/ 076526 group 0 – workshop accessories.
The centring pin No. 119019 is required when using the core drills No. 119010 and 119000.

Technical description

Nominal Ø D_C	16 mm
Cutting depth	35 mm
Tool material	Carbide
Colour ring	without
Type of product	Core drill

User data

	Suitability	V_c	ISO code
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm²	suitable		
Steel < 750 N/mm²	suitable		
Steel < 900 N/mm²	suitable		
Steel < 1100 N/mm²	suitable		
INOX < 900 N/mm²	suitable		
INOX > 900 N/mm²	suitable		
GG(G)	suitable		
CuZn	suitable		
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		