

# Kraftform Kompakt VDE 65 iS, PZ 2 x 154 mm

## Kraftform Kompakt VDE



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288164032 | <b>Size:</b>                  | 154x13x13 mm |
| <b>Part number:</b>    | 05003456001   | <b>Weight:</b>                | 30 g         |
| <b>Article number:</b> | KK 65 iS PZ   | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82054000     |

- Reduced shaft diameter and integrated insulation protection
- In this way, low-lying PZ screws can be accessed and actuated
- Insulated, individually tested as per IEC 60900
- 9 mm hex drive with with entry chamfer
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

Interchangeable blade with reduced shaft diameter and integrated insulation protection; this means that low-lying screws and spring elements can be accessed and actuated. Individually tested tools as per IEC 60900. Individual testing at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. The Wera Black Point tip offers a perfect fit and optimised corrosion protection.



### Web link

[https://products.wera.de/en/tools\\_by\\_trade\\_tools\\_for\\_electricians\\_kraftform\\_kompakt\\_vde\\_kk\\_65\\_is\\_pz.html](https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_kompakt_vde_kk_65_is_pz.html)

Wera - KK 65 iS PZ  
05003456001 - 4013288164032

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

# Kraftform Kompakt VDE 65 iS, PZ 2 x 154 mm




## Kraftform Kompakt VDE

### Individually tested



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

### VDE interchangeable blade with reduced shaft diameter




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

### VDE interchangeable blades 154 mm long



Suitable for Kraftform handles 7400 VDE, 827 T i and 817 VDE .

### Handle/interchangeable blade system – Kraftform Kompakt VDE



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

### Further versions in this product family:



mm



inch

05003455001<sup>1)</sup>

PZ 1

154

6 1/16"

05003456001<sup>1)</sup>

PZ 2

154

6 1/16"

<sup>1)</sup> Discontinued item

### Web link

[https://products.wera.de/en/tools\\_by\\_trade\\_tools\\_for\\_electricians\\_kraftform\\_kompakt\\_vde\\_kk\\_65\\_is\\_pz.html](https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_kompakt_vde_kk_65_is_pz.html)

Wera - KK 65 iS PZ  
05003456001 - 4013288164032

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de