Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 750mm

Order data

Order number	940861 750
GTIN	4062406070861
Item class	9GI

Description

Version:
Empty cabinet in 50×20G.
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene handle with a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.
Colour:
Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated.**
Note:
For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95.
According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	595 mm
Type of cabinet	Base cabinet
Height	750 mm
Depth in G	20
ComfortClose	no
Depth	500 mm

Electronic locking system can be retrofitted	yes
Width in G	50
Handle positioning	top
Weight	65 kg
Cabinet fronts	Plain sheet metal swing door
Width	1250 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11