Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 1000mm

Order data

Order number	940865 1000
GTIN	4062406071035
Item class	9GI

Description

Version:
Empty cabinet in 50×20G.
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene handle with a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.
Colour:
Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated.**
Note:
For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95.
According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1000 mm
Width	1250 mm
Cabinet fronts	Plain sheet metal sliding door
Usable height	845 mm
Width in G	50

Depth in G	20
Depth	500 mm
Handle positioning	top
Electronic locking system can be retrofitted	yes
Weight	78 kg
Type of cabinet	Base cabinet
ComfortClose	no
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Lock plate for GridLine Type GP21	914227 GP21