

Melamine Floor Pad

For daily cleaning and maintenance operations



Technical data sheet

TD149

Date: February 2013

Author : FG

Description:

The 3M Melamine Floor Pad has been developed for cleaning and maintenance of hard floors. It is composed of a special melamine foam composite material that creates a profile structure for improved cleaning and dirt-absorption effects.

Special Features:

- Cleans very well black marks, shoe marks, wheel marks as well as grease & oil residues (like sebum).
- Ideal for micro-porous surfaces such as ceramic, stoneware, marble, terrazzo, terracotta, polished and coated concrete, colovinyl tiles... Also works well on granite, plastics and linoleum.
- Ideal for shopping centers, swimming pools, warehouses...
- Cleans with very low abrasion on the floor.
- Better cleaning performance and durability than conventional non-structured melamine pads.
- Uneven structure of the pad goes around the irregularities of the floor, absorbs dirt with reduced clogging effect.
- Uses dry or with water only. Chemicals can also be added to improve cleaning.

Where and When to Use:

RPM	150-400	>400
Strip		
Deep	XX	

Scrub		
Spray	XX	
Scrubber dryer	XX	
Buff (dry)	XX	

XX Designed for X suitable

Use the 3M Scotch-Brite™ Melamine floor pad for routine maintenance procedures under standard floor machines (150 - 400 RPM). It can be used under a single disc machine or a scrubber dryer in wet conditions (water or chemicals) to clean the floor. In many cases, shine will also pop up. It can also be used in a spray cleaning operation. In many cases, shine will also pop up. It can also be used in dry conditions to clean light dirt. In many cases, shine will also pop up. *Always make a trial in a corner or a remote area first.*

Maintenance of pad:

In most of the cases, 3M Scotch-Brite™ Melamine floor pad does not need to be cleaned between usages.

However, in order to maximize its life and reduce risks of trapping hard particles, it is recommended dusting the pad or cleaning it under tap water.

Durability:

Durability highly depends on floor structure and method of use.

- Under single disk machines (wet): up to 1000 sqm.
- Under scrubber-dryers (wet): up to 10 000 sqm.

- In dry conditions: up to 500 sqm.
- Do not use strong acid or cleaning products containing chlorine.

Product Characteristics:

Colour: Grey & white

Note : color may vary without impacting cleaning performances and durability.

Backing: white polyester fleece backing for improved grip under the machine.

Marking: "3M" black logo on the back.

Weight: 1400 g/m²

Total Thickness: 30 mm

Melamine part thickness: 25 mm

Fleece part thickness: 5 mm

Centre hole: 85 mm diameter hole in fleece structure and 85 mm or 125 mm diameter hole in melamine structure

Aggressiveness (Schiefer Value):

Expected value for cleaning operation: from 0 to 0.17 g.

3M value: 0,08 gram

0	0,5	1	1,5	2	2,5
---	-----	---	-----	---	-----

Sizes:

Standard and non-standard sizes available on demand.

Packaging and labelling:

5 discs in a carton. Multilingual labels on every carton.

Disposal Informations:

Discard into appropriate container for incineration, if available. Packaging material: recyclable

Origin:

Made in Germany.