Garant GRIDLINE

Large-capacity top-mounted cabinet with plain sheet metal swing doors, Height: 1000mm

Order data

Order number	941031 1000
GTIN	4062406071523
Item class	9GI

Description

Version:
Equipped cabinet in 40×28G.
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.
Supplied with:
Cabinet with storage shelves.
Colour:
Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated.**
Note:
For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942583 and Group 95.
According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no

Usable height	845 mm
Handle positioning	bottom
Width in G	40
Electronic locking system can be retrofitted	yes
Number of shelves	1
Width	1000 mm
Depth in G	28
Depth	700 mm
Height	1000 mm
Weight	81 kg
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Top-mounted cabinet
Type of product	Large-capacity cabinet

Accessories

Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 200 mm	942573 200
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 75 mm	942573 75
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40

Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 100 mm	942573 100
Basic lighting set for GridLine cabinets withswing doors for cabinet height 900/1000 mm	940501 900/1000
Storage shelf with brackets100 kg for cabinet / compartment width in G 40	942530 40
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 300 mm	942573 300
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 125 mm	942573 125
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 150 mm	942573 150
Slide handle for GridLine Type GP11	914226 GP11
Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 1000/1250 mm	940511 1000/1250