HOLEX

Boring bar set, steel, without IC, right-hand, Type: SET07

Order data

Order number	260348 SET07
GTIN	4062406074982
Item class	29W

Description

Version:
Without through–coolant feed.
Supplied with:
Plastic case

Technical description

suitable indexable insert	DC..0702..
ISO code toolholder	S0810H SDUCR07; S1012K SDUCR07; S1216M SDUCR07
Pack of insert screws	269028 7
Minimum pre-drill ⌀ D_{min}	12 mm
Minimum pre-drill ⌀ D_{min}	15.5 mm
Minimum pre-drill ⌀ D_{min}	18 mm
Clamping height L_2	9 mm

Clamping height L_2	11 mm
Clamping height L_2	15 mm
Centre offset L_3	6.5 mm
Centre offset L_3	9 mm
Centre offset L_3	11 mm
Head length L_1	22.5 mm
Head length L_1	27.5 mm
Head length L_1	40.5 mm
Overall length L	100 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L_4	8 mm
Neck width L_4	10 mm
Neck width L_4	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Type of product	Boring bar