

Kraftform 2go 100, 11 pieces

Kraftform Plus – Series 100 VDE



EAN: 4013288187826
Part number: 05004310001
Article number: Kraftform 2go 100

Size: 185x115x240 mm
Weight: 1115 g
Country of origin: CZ
Customs tariff number: 82054000

- Insulated blades for secure work at 1,000 volts
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Lasertip tips for more secure fit in the screw head
- Hexagonal anti-roll feature against rolling away
- Suitable for docking with the Wera 2go system.

11 VDE-insulated, Kraftform screwdrivers; with "Take it easy" Toolfinder; in the Wera 2go 4 quiver; comes with an adjustable partition element for individual sectioning.

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_kraftform_2go_100.html

Wera - Kraftform 2go 100
05004310001 - 4013288187826



Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

At the workplace and when out and about



Wera 2go 4 Tool Quiver



The large set-down area improves the stability of the Tool Quiver. Its large handle means that the quiver can be easily transported or simply hung up at the workplace.

Robust and dimensionally stable




The robust and dimensionally stable material is very resistant against cuts and stabs. The tools carried are protected against damage and moisture. This enhances the service life of the tool box.

Clever organisation



The variably adjustable hook and loop fastener partition in the Tool Quiver ensures neat and tidy arrangement of the tools.

Perfect system supplement




Thanks to its hook and loop fastener zone, the Tool Quiver can be docked with the Wera 2go 1 tool carrier and with the Wera 2go 2 tool container.

Lasertip prevents slipping out




It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

"Take it easy" Tool Finder



Colour coding according to profile and size stamp. This enables faster and more reliable selection of the correct tool from the tool case.

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_kraftform_2go_100.html

Wera - Kraftform 2go 100
05004310001 - 4013288187826

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform 2go 100, 11 pieces

Kraftform Plus – Series 100 VDE

Set contents:

Wera 2go 4 Tool Quiver, 165 x 105 mm

05004353001 1x 165 x 105 mm



162 i PH VDE Insulated screwdriver for Phillips screws, PH 1 x 80 mm



05006152001 1x PH 1 x 80 mm
05006154001 1x PH 2 x 100 mm



165 i PZ VDE Insulated screwdriver for Pozidriv screws, PZ 1 x 80 mm



05006162001 1x PZ 1 x 80 mm
05006164001 1x PZ 2 x 100 mm



167 i VDE Insulated screwdriver for TORX® screws, TX 10 x 80 mm



05006170001 1x TX 10 x 80 mm
05006172001 1x TX 15 x 80 mm
05006174001 1x TX 20 x 80 mm



160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm



05006100001¹⁾ 1x 0.4 x 2.5 x 80 mm
05006116001 1x 0.8 x 4 x 150 mm
05006121001 1x 1 x 5.5 x 200 mm



1) without Lasertip

160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm



05006440001 1x 0.6 x 3.5 x 100 mm



Hook and Loop Fastener Strip 120, 120 x 50 mm

1x 120 x 50 mm



Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_kraftform_2go_100.html

Wera - Kraftform 2go 100
05004310001 - 4013288187826

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de