

190 i VDE Insulated nutdriver, 13 x 125 mm

Kraftform Plus – Series 100 VDE



EAN:	4013288032560	Size:	237x37x37 mm
Part number:	05005340001	Weight:	167 g
Article number:	190 i VDE	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Zinc phosphate plated

Wera VDE socket wrenches with multi-component Kraftform for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Individual testing at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.



Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_190_i_vde.html

Wera - 190 i VDE
05005340001 - 4013288032560

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Plus – Series 100 VDE

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_190_i_vde.html

Wera - 190 i VDE

05005340001 - 4013288032560

Wera Werkzeuge GmbH







Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Further versions in this product family:

						
	mm	inch	mm	mm	mm	inch
05005300001	5.5	-	125	98	11.0	5"
05005305001	6.0	-	125	98	12.0	5"
05005310001	7.0	-	125	105	14.0	5"
05005315001	8.0	-	125	105	15.0	5"
05005320001	9.0	-	125	105	16.0	5"
05005325001	10.0	-	125	112	17.0	5"
05005330001	11.0	-	125	112	19.0	5"
05005335001	12.0	-	125	112	20.0	5"
05005340001	13.0	-	125	112	21.0	5"

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_190_i_vde.html

Wera - 190 i VDE

05005340001 - 4013288032560

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de