

160 i/165 i/7 Rack Screwdriver set Kraftform Plus Series 100, single-pole phase tester and rack, 7 pieces
Kraftform Plus – Series 100 VDE



EAN:	4013288041715	Size:	280x205x55 mm
Part number:	05006148001	Weight:	666 g
Article number:	160 i/165 i/7 Rack	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Lasertip tips for more secure fit in the screw head

7-piece screwdriver set with individually tested, insulated screwdrivers as per IEC 60900. Individual testing at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially Lasertip: the tip literally bites itself into the screw head and prevents any slipping. "Take it easy" Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including single-pole phase tester and 1 rack for storage.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_160_i_165_i_7_rack.html

Wera - 160 i/165 i/7 Rack
05006148001 - 4013288041715

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Kraffform




The basic idea for the prototype of the Kraffform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraffform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Non-roll feature



All Kraffform screwdrivers have a non-roll feature at the lower end of the handle. The hexagonal design prevents any annoying rolling away of the screwdriver at the workplace.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraffform_plus_series_100_vde_160_i_165_i_7_rack.html

Wera - 160 i/165 i/7 Rack
 05006148001 - 4013288041715

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

160 i/165 i/7 Rack Screwdriver set Kraftform Plus Series 100, single-pole phase tester and rack, 7 pieces
Kraftform Plus – Series 100 VDE



Set contents:

165 i PZ VDE Insulated screwdriver for Pozidriv screws, PZ 1 x 80 mm



05006162001	1x	PZ 1 x 80 mm
05006164001	1x	PZ 2 x 100 mm

160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm



05006100001 ¹⁾	1x	0.4 x 2.5 x 80 mm
05006110001 ¹⁾	1x	0.6 x 3.5 x 100 mm
05006115001	1x	0.8 x 4 x 100 mm
05006120001	1x	1 x 5.5 x 125 mm

1) without Lasertip

247 Single-pole phase tester, 0.5 x 3 x 70 mm



05005655001 ¹⁾	1x	0.5 x 3 x 70 mm
---------------------------	----	-----------------

1) Product not available in the USA and Canada.

Product not available in the USA and Canada.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_160_i_165_i_7_rack.html

Wera - 160 i/165 i/7 Rack
05006148001 - 4013288041715

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de