

165 iS PZ/S # 1 + 2 Screwdriver set Kraftform Plus series 100. With reduced blade diameter, 2 pieces
Kraftform Plus – Series 100 VDE



| | | | |
|------------------------|---------------------|-------------------------------|---------------|
| EAN: | 4013288214317 | Size: | 225x100x40 mm |
| Part number: | 05006470001 | Weight: | 240 g |
| Article number: | 165 iS PZ/S # 1 + 2 | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Reduced shaft diameter: combination profile - Pozidriv/slotted



Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Combination profile - slotted and Pozidriv* particularly for jobs on terminal blocks, fuse boxes, switches and relays. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.


VDE-insulated screwdriver with reduced blade diameter

PlusMinus screwdrivers

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_165_is_pz_s__1__2.html

Wera - 165 iS PZ/S # 1 + 2
 05006470001 - 4013288214317

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

165 iS PZ/S # 1 + 2 Screwdriver set Kraftform Plus series 100. With reduced blade diameter, 2 pieces
Kraftform Plus – Series 100 VDE




Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle




Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

Non-roll feature



All Kraftform screwdrivers have a non-roll feature at the lower end of the handle. The hexagonal design prevents any annoying rolling away of the screwdriver at the workplace.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_165_is_pz_s__1__2.html

Wera - 165 iS PZ/S # 1 + 2
05006470001 - 4013288214317

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

165 iS PZ/S # 1 + 2 Screwdriver set Kraftform Plus series 100. With reduced blade diameter, 2 pieces
Kraftform Plus – Series 100 VDE



Set contents:

165 iS PZ/S VDE Insulated screwdriver with reduced blade diameter for PlusMinus screws (Pozidriv/slotted), # 1 x 80 mm



05006465001

1x # 1 x 80 mm

05006466001

1x # 2 x 100 mm

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_165_is_pz_s__1__2.html

Wera - 165 iS PZ/S # 1 + 2
05006470001 - 4013288214317

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de