The Zyklop Speed Ratchet, 3/8"
















EAN: 4013288220608 330x150x70 mm Size:

Part number: 05004175001 Weight: 1852 g Article number: Bicycle Set 7 Country of origin: CZ

> **Customs tariff** 82079030

number:



- Low return angle of only 5° for working in a small space
- Long bit sockets with extra slim, cylindrical profile zone for low-located couplings (e.g. for bottom bracket ball bearing or stem-
- 8790 HMB Deep socket wrench insert size 15 for use in cap socket couplings
- Sockets and bits for the most popular screw profiles for road bikes, mountain bikes and e-bikes
- Assortment in robust textile box with low weight for easy transport
- With adapter from 3/8" square head socket to ½" external square head for mounting special bicycle tools

27-piece 3/8" ratchet set for typical bicycle operations with extensive accessories:

1 Zyklop Speed ratchet with 3/8" drive, 10 Zyklop sockets, 2 Zyklop bit sockets with 30 mm and extra slim profile area for better accessibility in tight workspaces. With Take it easy tool finder: Colour coding by size. 1 Zyklop extension (short) with fast-rotating sleeve, 1 Wobble extension, 1 bit adapter, 1 connection part 3/8" external square head to 1/2" external square head, 10 bits, tough, for universal use. Incredibly compact set arrangement for many tools in a tight space thanks to the highly robust and durable textile box. Can be placed in an upright position for clearly arranged storage in the workshop shelf. Additional surface protection due to textile outer material. Low weight and small size for better mobility.























#### The Zyklop Speed Ratchet, 3/8"



#### Zyklop "6 in 1"

1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

### Pivots freely



The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

#### Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the freeturning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

# Simple direction change




All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

# Low return angle



The reversible ratchet with 72 finepitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

# 30 mm long and extra slim profile area



The bit sockets have a 30 mm long and extra slim profile area. This makes even couplings in tight work spaces easily accessible.

### The Zyklop sockets



The Zyklop sockets are suitable for manual and machine-operated tools (non impact). They feature a ball stop groove and knurling at the rear end for manageability during manual use. They are made of chrome-vanadium, dull chromed. Take it easy tool finder: Colour coding by size as well as size stamping - to help you find the required socket quickly and easily.

#### Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Web link

https://products.wera.de/en/ratchets\_and\_accessories\_the\_zyklop\_ratchets\_the\_zyklop\_ratchets\_3\_8\_the\_zyklop\_speed\_ratchet\_3\_8\_bicycle\_set\_7.html

#### The Zyklop Speed Ratchet, 3/8"



#### Set contents:

#### 8000 B Zyklop Speed Ratchet with 3/8" drive, 3/8" x 199 mm

05003550001 1x 3/8" x 199 mm



#### 8790 HMB Zyklop 3/8" socket, 6 x 29 mm



#### 8790 HMB Deep 3/8" socket, 15 x 64 mm

● 05004537001 1x 15 x 64 mm



#### 8740 B Zyklop Bit socket with 3/8" drive, with extra slim profile area, 8 x 100 mm

05003054001 1x 8 x 100 mm 05003056001 1x 10 x 100 mm

# 8794 B Zyklop wobble extension, 3/8", 3/8" x 76 mm

①5003584001 1x 3/8" x 76 mm



## 8784 B1 Zyklop bit adaptor, 3/8", 1/4" x 3/8" x 44 mm

①5003590001 1x 1/4" x 3/8" x 44 mm



# 8794 SB Zyklop extension with free-turning sleeve, short, 3/8", 3/8" x 125 mm

© 05003582001 1x 3/8" x 125 mm



#### 781 B 3/8" Connection parts, 781 B/C x 1/2 x 36 mm x 3/8"

05042673001 1x 781 B/C x 1/2 x 36 mm x 3/8"



Web link


 $https://products.wera.de/en/ratchets\_and\_accessories\_the\_zyklop\_ratchets\_the\_zyklop\_ratchets\_3\_8\_the\_zyklop\_speed\_ratchet\_3\_8\_bicycle\_set\_7.html$ 

# Bicycle Set 7, 27 pieces

# The Zyklop Speed Ratchet, 3/8"



#### 840/4 Z bits, 3 x 50 mm



1) Hexagonal blade

#### 867/4 7 TORX® bits. TX 10 x 50 mm

001/4 Z 1011/10 DIE, 17	Y TO X JO IIIIII		
$\odot$	05060132001	1x	TX 10 x 50 mm
₿ Wera	05060133001	1x	TX 15 x 50 mm
	05060134001	1x	TX 20 x 50 mm
	05060135001	1x	TX 25 x 50 mm
	05060136001	1x	TX 27 x 50 mm
	05060137001	1x	TX 30 x 50 mm