
Click-Torque adjustable torque wrenches with reversible ratchet





- 16-piece wrench set for bicycle applications with torque control including Wera Clique-Torque wrench A 5 (2.5-25 Nm)
- Sockets and bit sockets for the most popular screw profiles on road bikes, mountain bikes and e-bikes
- Easy setting and saving of the desired torque value with audible and tactile click when the scale value is reached (click 1)
- Safely quantified force: when the set value is reached, the torque wrench triggers audibly and noticeably (click 2)
- Precise to \pm 4% as per DIN EN ISO 6789-1:2017-07.

The 16-piece set from the screwdriving tool specialist Wera solves the most important screwdriving problems associated with bicycles, with reliable control of applied torque to protect sensitive components. With a click-torque wrench in the unmistakable Wera design. Very robust design with high accuracy as per DIN EN ISO 6789-1: 2017-07. Easy setting and saving of the default values. The audible and tactile snapping on reaching the scale values also facilitates the safe setting of the desired torque values. The robust release mechanism guarantees a clearly audible and tactile trigger signal when the set torque is reached. For clockwise torque-control and with a reversible 45-tooth ratchet. The torque wrench is extremely space-saving and supplemented with accessories that are suitable for the torque range and adapted to the most common screwed connections on bicycles; in a robust, surface-friendly textile box. Included are: Click Torque A 5, 1/4", 2.5 - 25 Nm, 4 sockets with 1/4" drive, 7 Hex Plus hexagon bit sockets and 4 TORX® bit sockets. Sockets and bit sockets with "Take it easy" tool finder with colour coding by size - for easy and quick location of the required tool. Bit sockets with holding function for extra comfortable screwdriving without the screw falling off the tool. Incredibly compact arrangement for a lot of tools in a small space. Textile box with very high robustness and longevity. Additional surface protection through the textile outer material. Low weight and volume for easier mobility. Bit sockets with all the benefits of Wera bit technology such as fitting accuracy, wear resistance and concentric run-out properties.





Click-Torque adjustable torque wrenches with reversible ratchet



For the road and the workshop

Click-Torque Wrench series

Exact



The Bicycle Set Torque 1 contains tools for the most popular screw profiles on road bikes, mountain bikes and e-bikes. With the included Click-Torque A torque wrench (2.5-25 Nm), even torquesensitive screwed connections can be loosened and tightened reliably. Clear and compact tool storage in the textile box.



wrench unmistakable Wera design.



Precise to \pm 4% as per DIN EN ISO 6789-1:2017-07.

Simple and safe




Easy setting and saving of the desired torque value; readable on the main and fine scales.

Simple setting



With audible and tactile clicks when adjusting the scale values.

Release mechanism



When the set torque value is reached, an audible and tactile mechanism triggers.

Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

Manual and machine sockets



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Web link

https://products.wera.de/en/torque_tools_series_click-torque_wrenches_click-torque_adjustable_torque_wrenches_with_reversible_ratchet_bicycle_set_torque_1.html

Wera - Bicycle Set Torque 1 05004180001 - 4013288207685

Click-Torque adjustable torque wrenches with reversible ratchet



Set contents:

Click-Torque A 5 torque wrench with reversible ratchet, 2.5-25 Nm, 1/4" x 2.5-25 Nm

1x 1/4" x 2.5-25 Nm

8790 HMA Zyklop 1/4" socket, 10 x 23 mm



 \mathbf{O}

05003509001
05003512001
05003513001
05003499001

05075604001

1x	10 x 23 mm
1x	13 x 23 mm
1x	14 x 23 mm
1x	15 x 23 mm

8767 A TORX® Zyklop bit socket, 1/4" drive, TX 10 x 28 mm

	05003390001	1x	TX 10 x 28
lo 6erc 667 A Femped	05003391001	1x	TX 20 x 28
	05003392001	1x	TX 25 x 28
876 Barlin	05003393001	1x	TX 30 x 28

8740 A HF Zyklop bit socket with holding function, 1/4" drive, 3 x 28 mm



1x	3 x 28 mm
1x	4 x 28 mm
1x	5 x 28 mm
1x	5 x 100 mm
1x	6 x 28 mm
1x	6 x 100 mm
1x	8 x 28 mm

mm mm mm mm

Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



Web link https://products.wera.de/en/torque_tools_series_click-torque_wrenches_click-torque_adjustable_torque_wrenches_with_reversible_ratchet_bicycle_set_torque_1.html