


Kraftform Kompakt Stubby magazine RA 4, 6 pieces



Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



EAN:	4013288221155	Size:	115x60x40 mm
Part number:	05008886001	Weight:	180 g
Article number:	Kraftform Kompakt Stubby Magazin RA 4	Country of origin:	CZ
		Customs tariff number:	82079030

- Short, compact Stubby shape for working in tight installation spaces, with 6 bits in the integrated magazine
- Ergonomic 2-component Kraftform handle for precise work
- Ratchet function with fine toothing for a low return angle and reversible ring (right, fixed, left)
- Captive and swiveling bit magazine for easy removal and safe storage of bits
- Tough viscous bits for universal use


Particularly small bitholding screwdriver with extremely short bit mounting for hard to reach areas. With ratchet function and fine toothing for a low return angle. Easy-to-operate reversible ring (right, fixed, left). Includes 6 tough, universal bits, which are located in a magazine in the handle. The strong permanent magnet in the bit mounting ensures secure holding of the bit. The 2-component Kraftform handle with the practical combination of hard and soft zones allows for a firm grip and precise working.

Compact shape



Particularly small bit hand-holder with extremely short bit mounting for hard to reach areas.

Handle with integrated bit magazine




The handle can be opened and thus gives access to the six bits contained in the magazine.

Swiveling bit magazine



The swiveling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

Ratchet functionality



The ratchet mechanism is fine-toothed for a low return angle. The screwdriving directions right/fixed/left can be set with the reversible ring. The magnetic bit mounting is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_4

Wera - Kraftform Kompakt Stubby Magazin RA 4
05008886001 - 4013288221155

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt Stubby magazine RA 4, 6 pieces

Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_4

Wera - Kraftform Kompakt Stubby Magazin RA 4
05008886001 - 4013288221155

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt Stubby magazine RA 4, 6 pieces

Kraftform Kompakt Stubby - With Kraftform bit-holding Stubby screwdriver handle.



Set contents:


851/1 Z bits, PH 1 x 25 mm



05072070001
05072072001

1x PH 1 x 25 mm
1x PH 2 x 25 mm

868/1 Z Square-Plus bits, # 1 x 25 mm



05066405001
05066410001

1x # 1 x 25 mm
1x # 2 x 25 mm

800/1 Z bits, 1 x 5.5 x 25 mm



05072059001
05072061001

1x 1 x 5.5 x 25 mm
1x 1.2 x 6.5 x 25 mm

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_stubby_with_kraftform_bit-holding_stubby_screwdriver_handle_kraftform_kompakt_stubby_magazin_ra_4

Wera - Kraftform Kompakt Stubby Magazin RA 4
05008886001 - 4013288221155

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de