

162 iSS PH VDE Insulated screwdriver with reduced blade diameter for Phillips screws, PH 1 x 80 mm
Kraftform Plus – Series 100 VDE



EAN:	4013288179432	Size:	161x26x26 mm
Part number:	05020131001	Weight:	35 g
Article number:	162 iSS	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Reduced blade and handle diameter

VDE insulated slotted screwdriver with reduced blade and handle diameter, suitable for actuating low-lying screws in particularly confined working spaces. Multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Individual testing at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.



Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_162_iss.html



Wera - 162 iSS
05020131001 - 4013288179432

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The super slim screwdrivers for Electricians

Individually tested

Impact strength test



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

The super slim screwdrivers for installation jobs in particularly confined spaces. Not only do the blades have a reduced diameter, the handles also have a very slim design.

The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.


Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle

Prevents hand injuries

Rapid hand repositioning

"Take it easy" Tool Finder



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_162_iss.html

Wera - 162 iSS
05020131001 - 4013288179432

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

162 iSS PH VDE Insulated screwdriver with reduced blade diameter for Phillips screws, PH 1 x 80 mm
Kraftform Plus – Series 100 VDE



Further versions in this product family:



mm



mm



inch

05020131001	PH 1	80	81	3 1/8"
05020133001	PH 2	100	98	4"

Web link

https://products.wera.de/en/tools_by_trade_tools_for_electricians_kraftform_plus_series_100_vde_162_iss.html

Wera - 162 iSS

05020131001 - 4013288179432

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de