


## 6001 Joker Switch Ratcheting combination wrench, with switch lever, 11 x 165 mm

### 6001 Joker Switch Ratcheting combination wrenches, with switch lever



<b>EAN:</b>	4013288183910	<b>Size:</b>	245x50x22 mm
<b>Part number:</b>	05020066001	<b>Weight:</b>	95 g
<b>Article number:</b>	6001 Joker Switch	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82041100

- Practical holding function thanks to the metal plate in the jaw
- Limit stop prevents any slipping
- Very fine toothing and robust locking element
- Ratchet end tilted by 15°
- With Take it easy tool finder: colour coding by size

Joker ratcheting combination wrenches with angled ratchet head and switch lever. The metal plate in the jaw provides for the holding function which reduces the risk of losing nuts and bolts. The integrated limit stop can prevent any slipping from the bolt head downwards and enables higher torque to be applied. The exchangeable metal plate in the jaw securely holds nuts and bolts with its extra hard teeth and reduces the risk of slipping. The double-hex geometry delivers a very positive connection with nuts or bolts and again provides for a lower risk of any slipping. The low return angle of only 30° at the jaw end avoids any time-consuming flipping of the wrench when fastening. The reversible ratchet mechanism at the ring end with its fine toothing (80 teeth) ensures great flexibility even in confined spaces. Audibly precise ratchet mechanism. Additionally, the robust two-piece locking element provides for an extreme stability. Comes with a 15° tilted ratchet end for secure work even at high torque. The special forged geometry allows for high torque transfer and high flexural rigidity. Manufactured out of high-performance chrome-molybdenum steel with a nickel-chromium coating for high corrosion protection. With "Take it easy" tool finder: colour coding according to size.



SWITCH



HOLDING  
FUNCTION



LIMIT  
STOP



ANTI-SLIP



30°  
SMALL  
ANGLE



TAKE IT EASY  
TOOL FINDER

#### Web link

[https://products.wera.de/en/joker\\_6001\\_joker\\_switch\\_ratcheting\\_combination\\_wrenches\\_with\\_switch\\_lever\\_6001\\_joker\\_switch.html](https://products.wera.de/en/joker_6001_joker_switch_ratcheting_combination_wrenches_with_switch_lever_6001_joker_switch.html)

Wera - 6001 Joker Switch  
05020066001 - 4013288183910

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Joker Switch



With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.



The direction of the fine-tooth ratchet mechanism can easily be changed via the smooth switch lever.

Tilted ratchet end



The ratchet end is tilted at 15° to the tool axis, making application of the tool in confined spaces much easier.

Ring ratchet spanner Joker 6000



The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately - no additional tools required.


**Web link**

[https://products.wera.de/en/joker\\_6001\\_joker\\_switch\\_ratcheting\\_combination\\_wrenches\\_with\\_switch\\_lever\\_6001\\_joker\\_switch.html](https://products.wera.de/en/joker_6001_joker_switch_ratcheting_combination_wrenches_with_switch_lever_6001_joker_switch.html)

Wera - 6001 Joker Switch  
05020066001 - 4013288183910

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Integrated limit-stop




Constant re-positioning of the wrench? Difficulty holding fasteners in confined spaces? Easing off to avoid any risks of injury or fastener damage? That was yesterday. Today, the Joker prevents slipping off of the fastener head with its integrated limit-stop - no longer is the thumb needed to act as a depth stop. This makes applications much easier and allows significantly more force to be applied during fastening jobs.

Double-hex geometry



The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts - it's a perfect fit. And the exchangeable, hardened metal gripping plate in the Joker's open end literally bites itself into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.

Small return angle



Instead of 60°, the Joker only has a 30° back-pivoting angle thanks to its unique double-hex design. Along with the Joker's straight neck, this means that flipping the wrench has become a thing of the past. With the Joker, you can now loosen and tighten nuts and bolts, in situations where conventional tools fail. Particularly in confined spaces, where conventional open-jawed wrenches cannot be used. The combination of limit stop and small return angle enables effective work, even on screw pipe connections.

"Take it easy" tool finder



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Further versions in this product family:



mm



mm



mm



mm



mm



mm

05020064001	luminous pink	8	144	20.3	5.5	18	7
05020065001	leuchtgelb_yello wC	10	159	23	5.5	21.5	7.5
<b>05020066001</b>	<b>cyan_2985C</b>	<b>11</b>	<b>165.0</b>	<b>24.3</b>	<b>6.3</b>	<b>22</b>	<b>7.5</b>
05020067001	schwarz_blackC	12	171	26.3	6.6	25	8.5
05020068001	tuerkis_339C	13	179	27.3	7	26	8.5
05020069001	pink_241C	14	187	30	7.5	28	9.5
05020070001	weiss	15	199	32	7.8	28.8	9.5
05020071001	violett_2735C	16	213	35	8.2	31.7	10.5
05020072001	rot_200C	17	225	37	8.5	33	10.5
05020073001	leuchtgruen_37 5C	18	234	39.5	9	34	11
05020074001	blau_307C	19	246	42	9.5	34.7	11

Web link

[https://products.wera.de/en/joker\\_6001\\_joker\\_switch\\_ratcheting\\_combination\\_wrenches\\_with\\_switch\\_lever\\_6001\\_joker\\_switch.html](https://products.wera.de/en/joker_6001_joker_switch_ratcheting_combination_wrenches_with_switch_lever_6001_joker_switch.html)

Wera - 6001 Joker Switch  
05020066001 - 4013288183910

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de