



EAN:	4013288219480	Size:	160x18x18 mm
Part number:	05030114001	Weight:	14 g
Article number:	1567 TORX® B0 ESD Micro	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Micro screwdriver for recessed TORX® screws with safety pin
- ESD-safe tool thanks to surface resistance of $\leq 10^9$ Ohm
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- Anti-roll feature and swivel cap for rapid twisting

ESD-safe Micro screwdriver. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



Web link

https://products.wera.de/en/screwdrivers_esd_series_1567_torx_bo_esd_micro.html

Wera - 1567 TORX® B0 ESD Micro
05030114001 - 4013288219480

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Wera ESD Tools

High protection

Kraftform Micro handle

The power zone




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.



Multi-component screwdriver handle for ergonomic working.




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone


The precision zone

Wera Black Point tip


"Take it easy" Tool Finder




The fast-turning zone just below the rotating cap allows rapid twisting.



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Further versions in this product family:

		mm	mm	mm	inch
05030113001	TX 6 B0	60	97	3.0	2 3/8"
05030114001	TX 8 B0	60	97	3.0	2 3/8"

Web link

https://products.wera.de/en/screwdrivers_esd_series_1567_torx_bo_esd_micro.html

Wera - 1567 TORX® B0 ESD Micro
05030114001 - 4013288219480

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de