

## ESD Series



<b>EAN:</b>	4013288194756	<b>Size:</b>	140x19x19 mm
<b>Part number:</b>	05030135001	<b>Weight:</b>	11 g
<b>Article number:</b>	1567 TORX PLUS® IPR ESD	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Kraftform Micro screwdriver for recessed IPR TORX PLUS® screws
- ESD-safe tool thanks to surface resistance of  $\leq 10^9$  Ohm
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- Anti-roll feature and swivel cap for rapid twisting

High quality Wera Micro screwdriver for precision mechanical jobs. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit. The electric surface resistance of the Wera ESD material is  $\leq 10^9$  ohm. This securely protects components against electrostatic energy and associated damage. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



## Web link

[https://products.wera.de/en/screwdrivers\\_esd\\_series\\_1567\\_torx\\_plus\\_ipr\\_esd.html](https://products.wera.de/en/screwdrivers_esd_series_1567_torx_plus_ipr_esd.html)

Wera - 1567 TORX PLUS® IPR ESD  
 05030135001 - 4013288194756

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de


ESD Series

Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

“Take it easy” Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

Further versions in this product family:

	 No image available				
		mm	mm	mm	inch
05030135001 <sup>1)</sup>	1 IPR	40	97	2.0	1 9/16"

<sup>1)</sup> Without bore hole

Web link

[https://products.wera.de/en/screwdrivers\\_esd\\_series\\_1567\\_torx\\_plus\\_ipr\\_esd.html](https://products.wera.de/en/screwdrivers_esd_series_1567_torx_plus_ipr_esd.html)

Wera - 1567 TORX PLUS® IPR ESD  
05030135001 - 4013288194756

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de