ESD Series









EAN: 4013288113900 **Size:** 260x205x55 mm

 Part number:
 05030170001
 Weight:
 408 g

 Article number:
 1578 A/6
 Country of origin:
 CZ

Customs tariff 82054000

number:

- Kraftform Micro screwdriver set for slotted and cross-recess screws, Phillips
- ESD-safe tool thanks to surface resistance of \leq 10⁹ 0hm
- Multi-component Kraftform Micro handles for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

ESD-safe Wera Micro screwdriver set. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit.

















ESD Series



Wera ESD Tools

EPA

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection




The electric surface resistance of the Wera ESD material is $\leq 10 < \text{sup} > 9 < / \text{sup} > \text{ ohm.}$ This securely protects components against electrostatic energy and associated damage.

Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link https://products.wera.de/en/screwdrivers_esd_series_1578_a_6.html

1578 A/6 ESD Screwdriver set and rack for electronic applications, 6 pieces

ESD Series



Set contents:

1550 PH ESD Kraftform Micro screwdriver for Phillips screws, PH 0 x 60 mm

05030111001¹⁾ 1x PH 0 x 60 mm
05030112001 1x PH 1 x 80 mm
1) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)

1578 A ESD Kraftform Micro screwdriver for slotted screws, 0.25 x 1.2 x 40 mm

_	

		o, oo
05030100001	1x	0.25 x 1.2 x 40 mm
05030101001	1x	0.23 x 1.5 x 40 mm
05030102001	1x	0.30 x 1.8 x 60 mm
05030104001	1x	0.40 x 2.5 x 80 mm