

1550/6 ESD Screwdriver set and rack for electronic applications, 6 pieces



ESD Series



| | | | |
|------------------------|---------------|-------------------------------|---------------|
| EAN: | 4013288194787 | Size: | 250x205x50 mm |
| Part number: | 05030180001 | Weight: | 341 g |
| Article number: | 1550/6 ESD | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |

- ESD-safe tool thanks to surface resistance of $\leq 10^9$ Ohm
- The fast-turning zone just below the rotating cap allows rapid twisting.
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Multi-component Kraffform Micro handles for fast and ergonomic screwdriving
- Includes practical rack for tidy storage of the screwdrivers

ESD-safe Wera Micro screwdriver set. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit.



Web link
https://products.wera.de/en/screwdrivers_esd_series_1550_6_esd.html

Wera - 1550/6 ESD
05030180001 - 4013288194787

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

ESD Series

Wera ESD Tools



When doing screwdriving jobs on electronic components (like e.g. smartphones and tablet PCs), there should be no electrostatic discharge as this could cause malfunctions and a complete failure. Therefore, tools that are secure against electrostatic discharge are indispensable.




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection




The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_esd_series_1550_6_esd.html

Wera - 1550/6 ESD
05030180001 - 4013288194787

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

1550/6 ESD Screwdriver set and rack for electronic applications, 6 pieces



ESD Series

Set contents:

1550 PH ESD Kraftform Micro screwdriver for Phillips screws, PH 000 x 40 mm



05030117001^{1),2)} 1x PH 000 x 40 mm

05030118001^{1),2)} 1x PH 00 x 40 mm

05030119001³⁾ 1x PH 0 x 40 mm

1) Optimised for Asian PH screws

2) On the output side, the blade is turned to a nominal length of 10 mm

3) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)

1578 A ESD Kraftform Micro screwdriver for slotted screws, 0.35 x 2.5 x 40 mm



05030108001 1x 0.35 x 2.5 x 40 mm

1567 IPR TORX PLUS® ESD screwdriver, 1 IPR x 40 mm



05030135001¹⁾ 1x 1 IPR x 40 mm

1) Without bore hole

1572 ESD Kraftform Micro screwdriver for Microstix® screws, m x 40 mm



05030080001 1x m x 40 mm

Web link

https://products.wera.de/en/screwdrivers_esd_series_1550_6_esd.html

Wera - 1550/6 ESD

05030180001 - 4013288194787

Wera Werkzeuge GmbH

Korzterter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de