

Kraftform Kompakt 60 RA, Imperial, 17 pieces

Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.



EAN:	4013288155306	Size:	190x135x55 mm
Part number:	05051041001	Weight:	545 g
Article number:	KK 60 RA Imperial	Country of origin:	CZ
		Customs tariff number:	82079030

- Suitable for manual and power tool operations
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Ratchet functionality
- Fine-pitched teeth for small return angle; switchover ring (right, fixed, left)
- Maximum torque of up to 50 Newton metres

17-piece set with bits in a length of 89 mm in a practical pouch. 1 holder 816 RA Kraftform with ratchet function: fine-toothing for a small return angle, switchover ring (right, fixed, left), maximum torque of up to 50 Newton metres. 1/4" hexagon socket head take-up and Rapidaptor technology for low-fatigue working and rapid bit change; magnetic. Can also be used directly with a power tool.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra_imperial.html

Wera - KK 60 RA Imperial
05051041001 - 4013288155306

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt 60 RA, Imperial, 17 pieces



Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.

816 RA Ratchet screwdriver



Ratchet screwdriver, fine-tooth design for minimal return angle, switchover ring (right, locked, left), maximum torque of up to 50 Newton metres, 1/4" hexagon chuck with Rapidaptor technology i.e. rapid-in, rapid-out, rapid-spin, chuck-all and single-hand function for rapid bit change, magnetic, suitable for hexagon socket insert bits as per DIN ISO 1173-C 6.3 and E 6.3 and Wera series 1 and 4

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Fine adjustment work




Additionally, the lockable neutral position permits exact adjustment work without having to change the screwdriving direction every time. Lockable neutral position for fine adjustment work.

Changing ratchet direction




Ergonomic design of the reverse direction switch.

Fine-tooth design



Fine action 44 tooth system for precision work. Great time savings when screwdriving.

Chuck-all




The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra_imperial.html

Wera - KK 60 RA Imperial
05051041001 - 4013288155306

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt 60 RA, Imperial, 17 pieces

Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.



Set contents:

816 RA Ratchet screwdriver, 1/4" x 142 mm



05051461001 1x 1/4" x 142 mm



851/4 Z bits, PH 1 x 89 mm



05059760001 1x PH 1 x 89 mm

05059775001 1x PH 2 x 89 mm

05059795001¹⁾ 1x PH 3 x 89 mm

1) Hexagonal blade

867/4 Z TORX® B0 bits with bore hole, TX 10 x 89 mm



05060050001 1x TX 10 x 89 mm

05060051001 1x TX 15 x 89 mm

05060052001 1x TX 20 x 89 mm

05060053001 1x TX 25 x 89 mm

05060054001 1x TX 30 x 89 mm

800/4 Z bits, 1 x 5.5 x 89 mm



05059488001 1x 1 x 5.5 x 89 mm



840/4 Z bits, 3/32" x 89 mm



05059661001 1x 3/32" x 89 mm

05059663001 1x 1/8" x 89 mm

05059665001 1x 5/32" x 89 mm

05059666001 1x 3/16" x 89 mm

868/4 Square-Plus bits, # 1 x 89 mm



05134800001 1x # 1 x 89 mm

05134801001 1x # 2 x 89 mm

05134802001 1x # 3 x 89 mm



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_with_ratchet_function_fine_tooth_system_for_precision_work_kk_60_ra_imperial.html

Wera - KK 60 RA Imperial
05051041001 - 4013288155306

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de