Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.











EAN: 4013288156280 **Size:** 150x64x47 mm

Part number:05051461001Weight:204 gArticle number:816 RACountry of origin:CZ

Customs tariff 84661038

number:

- Ratcheting screwdriver with Rapidaptor technology for rapid bit change
- Ratchet with fine-pitched toothing for a low return angle
- Switchover (right, fixed, left)
- Maximum torque of up to 50 Newton metres
- Multi-component Kraftform handle for fast and ergonomic screwdriving

High quality bit holder. Includes a ratchet: fine-toothing with a small return angle, switchover (right, fixed, left), maximum torque of up to 50 Newton metres. The Rapidaptor quick-release chuck enables rapid bit change without needing any special tools. The strong permanent magnet holds the bits absolutely securely. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Suitable for bits with ¼" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.



816 RA Ratchet screwdriver



Ratchet screwdriver, fine-tooth design for minimal return angle, switchover ring (right, locked, left), maximum torque of up to 50 Newton metres, 1/4" hexagon chuck with Rapidaptor technology i.e. rapid-in, rapid-out, rapid-spin, chuck-all and single-hand function for rapid bit change, magnetic, suitable for hexagon socket insert bits as per DIN ISO 1173-C 6.3 and E 6.3 and Wera series 1 and 4

Fine-tooth design



Fine action 44 tooth system for precision work. Great time savings when screwdriving.

Fine adjustment work



Additionally, the lockable neutral position permits exact adjustment work without having to change the screwdriving direction every time. Lockable neutral position for fine adjustment work.

Changing ratchet direction



Ergonomic design of the reverse direction switch.

Chuck-all



The Rapidaptor quick-release chucks hold ¼" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Rapid-spin



The free-turning sleeve allows screw steadying at the start of the screwdriving process. This makes it easier to apply the tool to the screw and prevents slipping. It can also be used as a short extension for 1/4" applications e.g. in combination with the Wera Zyklop Ratchets.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_with_ratchet_function_fine_tooth_system_for_precision_work_816_ra.html

816 RA Ratchet screwdriver, 1/4" x 142 mm

Kraftform Kompakt with Ratchet Function - Fine tooth system for precision work.



Further versions in this product family:

	0	\(\frac{1}{V} \)
	inch	mm
05051461001	1/4"	142.0

Web link

 $https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_with_ratchet_function_fine_tooth_system_for_precision_work_816_ra.html$