


395 Nutdriver, 5 x 125 mm

Kraftform Plus – Series 300



EAN:	4013288004772	Size:	223x33x33 mm
Part number:	05028225001	Weight:	71 g
Article number:	395	Country of origin:	CZ
		Customs tariff number:	82054000

- Nutsetter for hexagon head screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Chrome-plated

High quality nutsetter by Wera. Multi-component Kraftform handle for high working speeds and particularly ergonomic screwdriving. Kraftform Plus: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Hexagonal anti-roll feature prevents any rolling away and handle markings make for simplified finding and sorting of the tool; for hexagon head screws.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395.html

Wera - 395
05028225001 - 4013288004772

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Large contact area



The large contact area - with particularly high friction to the soft zones - results in high torque transfer without any bruising from the edges.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.






Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395.html

Wera - 395
05028225001 - 4013288004772

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

					
	mm	mm	mm	mm	inch
05028205001	3.0	125	98	5.0	5"
05028210001	3.5	125	98	6.1	5"
05028215001	4.0	125	98	6.9	5"
05028220001	4.5	125	98	7.1	5"
05028225001	5.0	125	98	8.1	5"
05028230001	5.5	125	98	8.1	5"
05029405001	6.0	125	98	9.1	5"
05029410001	7.0	125	105	11.0	5"
05029415001	8.0	125	105	12.1	5"
05029420001	9.0	125	105	13.1	5"
05029425001	10.0	125	112	14.1	5"
05029430001	11.0	125	112	16.0	5"
05029435001	12.0	125	112	17.1	5"
05029440001	13.0	125	112	18.1	5"
05029445001	14.0	125	112	19.1	5"
05029450001	15.0	125	112	21.0	5"

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395.html

Wera - 395

05028225001 - 4013288004772

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de