

395 H0 Nutdriver, 3/8" x 90 mm

Kraftform Plus – Series 300



EAN:	4013288110541	Size:	192x40x40 mm
Part number:	05029505001	Weight:	106 g
Article number:	395 H0	Country of origin:	CZ
		Customs tariff number:	82054000

- Nutsetter for hexagon head screws
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Hollow shaft for protruding threaded rods, chrome-plated

Premium Wera insert wrench screwdriver with hollow shaft for screwdriving on thread rods, because only then can the thread rod penetrate through the bolt into the hollow shaft of the screwdriver. Multi-component Kraftform handle for high working speeds and particularly ergonomic screwdriving. Kraftform Plus: Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. With hexagon anti-roll protection against rolling away. Handles marked for easy identification and sorting of tools. For external hexagon screws.



Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395_ho.html

Wera - 395 H0
05029505001 - 4013288110541

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hollow shaft nutsetter



Hollow shaft for protruding threaded rods



A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.

Kraftform



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Large contact area



The large contact area - with particularly high friction to the soft zones - results in high torque transfer without any bruising from the edges.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Identification marking



The screw symbol and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.







Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395_ho.html

Wera - 395 HO
05029505001 - 4013288110541

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

						
	mm	inch	mm	mm	mm	inch
05029460001	5.0	-	90	98	7.2	3 35/64"
05029461001	5.5	-	90	98	7.2	3 35/64"
05029462001	6.0	-	90	98	7.2	3 35/64"
05029463001	7.0	-	90	105	7.2	3 35/64"
05029464001	8.0	-	90	105	9.3	3 35/64"
05029465001	10.0	-	90	112	9.3	3 35/64"
05029466001	13.0	-	90	112	11.0	3 35/64"
05029501001	-	3/16"	90	98	7.2	3 35/64"
05029502001	-	1/4"	90	98	7.2	3 35/64"
05029503001	-	5/16"	90	105	9.3	3 35/64"
05029504001	-	11/32"	90	105	9.3	3 35/64"
05029505001	-	3/8"	90	112	9.3	3 35/64"
05029506001	-	7/16"	90	112	11.0	3 35/64"
05029507001	-	1/2"	90	112	11.0	3 35/64"

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_395_ho.html

Wera - 395 HO

05029505001 - 4013288110541

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de