### 1572 ESD Kraftform Micro screwdriver for Microstix® screws, 00 x 40 mm

#### **ESD Series**







**EAN:** 4013288181176 **Size:** 157x13x13 mm

Part number:05030081001Weight:13 gArticle number:1572 ESDCountry of origin:CZ

Customs tariff 82054000

number:

• Screwdriver for Microstix® screws

• ESD-safe tool thanks to surface resistance of  $\leq$  10<sup>9</sup>0hm

• Ergonomic Kraftform handle for pleasant and low-fatigue working

• The Wera Black Point tip offers an exact fit and optimum corrosion protection

• Take it easy tool finder: colour coding according to profile and size

· Hexagonal anti-roll feature against rolling away

ESD-safe screwdriver for Microstix® screws. Dependable protection against electrostatic energy and associated damage. Comes with an ergonomic Kraftform Micro handle for pleasant and low-fatigue working and Black Point tip for high corrosion protection. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.

















#### **ESD Series**



#### Wera ESD Tools

# EPA

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

# **High protection**




The electric surface resistance of the Wera ESD material is  $\leq 10 < \text{sup} > 9 < / \text{sup} > 0 \text{ hm}$ . This securely protects components against electrostatic energy and associated damage.

#### Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

#### The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

#### The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

# The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

# Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

# "Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link https://products.wera.de/en/screwdrivers\_esd\_series\_1572\_esd.html

# 1572 ESD Kraftform Micro screwdriver for Microstix® screws, 00 x 40 mm

# **ESD Series**



# Further versions in this product family:

		<b>\  \  \  \  \  \  \  \  \  \  \  \  \  \</b>	A V	$\varnothing$	A v
		mm	mm	mm	inch
05030080001	m	40	97	2.5	1 9/16"
05030081001	00	40	97	2.5	1 9/16"
05030082001	F	40	97	2.5	1 9/16"
05030083001	0	40	97	2.5	1 9/16"
05030084001	1	40	97	2.5	1 9/16"