

1572 ESD Krafftform Micro screwdriver for Microstix® screws, 0 x 40 mm



ESD Series



EAN:	4013288181190	Size:	157x13x13 mm
Part number:	05030083001	Weight:	13 g
Article number:	1572 ESD	Country of origin:	CZ
		Customs tariff number:	82054000

- Screwdriver for Microstix® screws
- ESD-safe tool thanks to surface resistance of $\leq 10^{9\Omega}$
- Ergonomic Krafftform handle for pleasant and low-fatigue working
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away

ESD-safe screwdriver for Microstix® screws. Dependable protection against electrostatic energy and associated damage. Comes with an ergonomic Krafftform Micro handle for pleasant and low-fatigue working and Black Point tip for high corrosion protection. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



Web link
https://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD
05030083001 - 4013288181190

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

ESD Series

Wera ESD Tools

High protection

Kraftform Micro handle

The power zone




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.



The electric surface resistance of the Wera ESD material is $\leq 10^{10}$ ohm. This securely protects components against electrostatic energy and associated damage.



Multi-component screwdriver handle for ergonomic working.




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The precision zone


The fast-turning zone

Rotating cap and fast-turning zone


“Take it easy” Tool Finder




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.



The fast-turning zone just below the rotating cap allows rapid twisting.



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD

05030083001 - 4013288181190

Wera Werkzeuge GmbH






Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Further versions in this product family:

		 mm	 mm	 mm	 inch
05030080001	m	40	97	2.5	1 9/16"
05030081001	00	40	97	2.5	1 9/16"
05030082001	F	40	97	2.5	1 9/16"
05030083001	0	40	97	2.5	1 9/16"
05030084001	1	40	97	2.5	1 9/16"

Web link

https://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD

05030083001 - 4013288181190

Wera Werkzeuge GmbH

Korzeter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de