

# Kraftform Kompakt VDE 15 Torque 1.2-3.0 Nm extra slim 1, 15 pieces

Series 7400 Insulated Kraftform Torque Screwdrivers



<b>EAN:</b>	4013288168375	<b>Size:</b>	225x150x80 mm
<b>Part number:</b>	05059291001	<b>Weight:</b>	760 g
<b>Article number:</b>	Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Kraftform Kompakt VDE torque screwdriver set with adjustable torque
- Adjustable Kraftform VDE torque holder exclusively for Wera VDE interchangeable blades
- VDE interchangeable blades 154 mm long
- In robust pouch
- 15-piece

15-piece torque VDE interchangeable blade set. Includes 14 blades (12 of which with a reduced diameter) with integrated insulation protection. Torque VDE holder with adjustable torque from 1.2-3.0 Nm. Kraftform Plus handle: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer.



## Web link

[https://products.wera.de/en/torque\\_tools\\_insulated\\_torque\\_tools\\_series\\_7400\\_insulated\\_kraftform\\_torque\\_screwdrivers\\_kraftform\\_kompakt\\_vde\\_15\\_torque\\_1\\_2-3\\_0\\_nm\\_extra](https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra)

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1  
05059291001 - 4013288168375

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

**Individually tested**




Kraftform adjustable torque handle for Electricians



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

**Handle/interchangeable blade system – Kraftform Kompakt VDE**



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

**Kraftform adjustable torque handle for Electricians**



Easy-to-read scale value. Measurement accuracy is  $\pm 6\%$  in accordance with the standard EN ISO 6789.

**Kraftform adjustable torque handle for Electricians**




Simple setting of the required torque by hand.

**Excess-load signal**




Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

**Inserting the blade**



According to the job, the insulated inter-changeable blade with the required tipstyle, or a switch cabinet key is inserted into the clamping mechanism.

**Taking out the blade**



By pulling and holding down the clamping sleeve the interchangeable screwdriver blade, or the switch cabinet key, is unlocked and can easily be taken out of the handle.

**Web link**

[https://products.wera.de/en/torque\\_tools\\_insulated\\_torque\\_tools\\_series\\_7400\\_insulated\\_kraftform\\_torque\\_screwdrivers\\_kraftform\\_kompakt\\_vde\\_15\\_torque\\_1\\_2-3\\_0\\_nm\\_extra](https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra)

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1  
05059291001 - 4013288168375

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

# Kraftform Kompakt VDE 15 Torque 1.2-3.0 Nm extra slim 1, 15 pieces



## Series 7400 Insulated Kraftform Torque Screwdrivers


### Set contents:


#### Series 7400 VDE Kraftform adjustable torque handle (0.3-3.5 Nm), 7441 VDE x 1.2-3.0 Nm

 05074750001 1x 7441 VDE x 1.2-3.0 Nm




#### Kraftform Kompakt VDE 62 iS, PH 1 x 154 mm


 05003413001<sup>1)</sup> 1x PH 1 x 154 mm

 05003414001<sup>1)</sup> 1x PH 2 x 154 mm

1) Discontinued item


#### Kraftform Kompakt VDE 65 iS, PZ 1 x 154 mm


 05003455001<sup>1)</sup> 1x PZ 1 x 154 mm

 05003456001<sup>1)</sup> 1x PZ 2 x 154 mm

1) Discontinued item


#### Kraftform Kompakt VDE 65 iS PZ/S, # 1 x 154 mm

 05003447001<sup>1)</sup> 1x # 1 x 154 mm

 05003448001<sup>1)</sup> 1x # 2 x 154 mm

1) Discontinued item


#### Kraftform Kompakt VDE 67 i TORX®, TX 10 x 154 mm


 05003431001<sup>1)</sup> 1x TX 10 x 154 mm

1) Discontinued item

#### Kraftform Kompakt VDE 67 iS TORX®, TX 15 x 154 mm


 05003437001<sup>1)</sup> 1x TX 15 x 154 mm

 05003438001<sup>1)</sup> 1x TX 20 x 154 mm

 05003439001<sup>1)</sup> 1x TX 25 x 154 mm


1) Discontinued item


#### Kraftform Kompakt VDE 60 i, 0.4 x 2.5 x 154 mm


 05003400001<sup>1)</sup> 1x 0.4 x 2.5 x 154 mm

1) Discontinued item

#### Kraftform Kompakt VDE 60 iS, 0.6 x 3.5 x 154 mm

 05003406001<sup>1)</sup> 1x 0.6 x 3.5 x 154 mm

 05003407001<sup>1)</sup> 1x 0.8 x 4 x 154 mm

 05003408001<sup>1)</sup> 1x 1 x 5.5 x 154 mm

1) Discontinued item

Discontinued item

### Web link

[https://products.wera.de/en/torque\\_tools\\_insulated\\_torque\\_tools\\_series\\_7400\\_insulated\\_kraftform\\_torque\\_screwdrivers\\_kraftform\\_kompakt\\_vde\\_15\\_torque\\_1\\_2-3\\_0\\_nm\\_extra\\_slim\\_1](https://products.wera.de/en/torque_tools_insulated_torque_tools_series_7400_insulated_kraftform_torque_screwdrivers_kraftform_kompakt_vde_15_torque_1_2-3_0_nm_extra_slim_1)

Wera - Kraftform Kompakt VDE 15 Torque 1,2-3,0 Nm extra slim 1  
05059291001 - 4013288168375

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de