#### 1569 ESD Nutdriver Kraftform Micro, 2 x 60 mm

#### **ESD Series**







**EAN:** 4013288184061 **Size:** 157x13x13 mm

Part number:05030412001Weight:19 gArticle number:1569 ESDCountry of origin:CZ

Customs tariff 82054000

number:

• Kraftform Micro screwdriver for hexagon head screws

- ESD-safe tool thanks to surface resistance of  $\leq$  10<sup>9</sup> 0hm
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Kraftform Micro handle with swivel cap for rapid twisting
- Take it easy tool finder: colour coding according to profile and size
- · Hexagonal anti-roll feature against rolling away

ESD-safe Micro screwdriver. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.















#### **ESD Series**



#### Wera ESD Tools

# EPA

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

#### **High protection**




The electric surface resistance of the Wera ESD material is  $\leq$  10<sup>9</sup> ohm. This securely protects components against electrostatic energy and associated damage.

#### Kraftform Micro handle



Multi-component screwdriver handle for ergonomic working.

#### The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

#### The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

# Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

# "Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link https://products.wera.de/en/screwdrivers\_esd\_series\_1569\_esd.html

# 1569 ESD Nutdriver Kraftform Micro, 2 x 60 mm

## **ESD Series**



## Further versions in this product family:

		A	A V	$\varnothing$	A v
		mm	mm	mm	inch
05030410001	1.5	60	97	5.7	2 3/8"
05030411001	1.8	60	97	5.7	2 3/8"
05030412001	2.0	60	97	5.7	2 3/8"
05030413001	2.5	60	97	5.7	2 3/8"
05030414001	3.0	60	97	5.7	2 3/8"
05030415001	3.2	60	97	5.7	2 3/8"
05030416001	3.5	60	97	5.7	2 3/8"
05030417001	4.0	60	97	5.7	2 3/8"
05030418001	4.5	60	97	6.4	2 3/8"
05030150001	5.0	60	97	7.0	2 3/8"
05030151001	5.5	60	97	7.8	2 3/8"