## 1569 ESD Nutdriver Kraftform Micro, 2.5 x 60 mm

#### **ESD Series**



- Kraftform Micro screwdriver for hexagon head screws
- ESD-safe tool thanks to surface resistance of  $\leq 10 < sup > 9 < /sup > 0hm$
- · Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Kraftform Micro handle with swivel cap for rapid twisting
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away

ESD-safe Micro screwdriver. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.







05030413001 - 4013288184078

### **ESD Series**



#### Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

### High protection




The electric surface resistance of the Wera ESD material is  $\leq$  10<sup>9</sup> ohm. This securely protects components against electrostatic energy and associated damage.

#### Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

#### The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

#### The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

# Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes timeconsuming grip adjustments as with other conventional precision screwdrivers unnecessary.





Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

## 1569 ESD Nutdriver Kraftform Micro, 2.5 x 60 mm

**ESD Series** 



Further versions in this product family:

|             |     | ∏ <b>↓</b><br>mm | ∭ Å<br>▼ | Mm  |        |
|-------------|-----|------------------|----------|-----|--------|
|             |     |                  |          |     |        |
| 05030410001 | 1.5 | 60               | 97       | 5.7 | 2 3/8" |
| 05030411001 | 1.8 | 60               | 97       | 5.7 | 2 3/8" |
| 05030412001 | 2.0 | 60               | 97       | 5.7 | 2 3/8" |
| 05030413001 | 2.5 | 60               | 97       | 5.7 | 2 3/8" |
| 05030414001 | 3.0 | 60               | 97       | 5.7 | 2 3/8" |
| 05030415001 | 3.2 | 60               | 97       | 5.7 | 2 3/8" |
| 05030416001 | 3.5 | 60               | 97       | 5.7 | 2 3/8" |
| 05030417001 | 4.0 | 60               | 97       | 5.7 | 2 3/8" |
| 05030418001 | 4.5 | 60               | 97       | 6.4 | 2 3/8" |
| 05030150001 | 5.0 | 60               | 97       | 7.0 | 2 3/8" |
| 05030151001 | 5.5 | 60               | 97       | 7.8 | 2 3/8" |

05030413001 - 4013288184078