



EAN:	4013288214584	Size:	115x100x62 mm
Part number:	05057472001	Weight:	212 g
Article number:	Kraftform Kompakt Stubby ESD 1	Country of origin:	CZ
		Customs tariff number:	82079030

- Handle/Interchangeable blade system for rapid exchange of the blade
- Stubby ESD bit hand holder: short compact shape for working in confined spaces
- ESD bits hand holder for electrostatically safe working, magnetic
- Ergonomic 2-component Kraftform handle for precise work
- 851/1 J: bits optimized for Asian PH screws

Handle/interchangeable blade system for lightning fast replacement of the required blade. Especially small ESD bit-holding Stubby screwdriver handle with short blade for electrostatically secure working even in hard to reach areas. Suitable for the mounting of bits with ¼" hexagon drive as per DIN ISO 1173-C 6.3 and Wera connection series 1. With strong permanent magnet, which also holds large and heavy screws. The 2-component Kraftform handle with its practical combination of hard and soft zones allows for a firm grip and precise working. High-quality bits for universal use. Compact, textile box with high robustness, low weight and volume. Suitable for docking with the Wera 2go system.

Web link

https://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_stubby_esd_1.html

Wera - Kraftform Kompakt Stubby ESD 1
05057472001 - 4013288214584

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

ESD Series

Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Tangible ergonomics



The 2-component Kraftform handle allows high power transmission due to the non-slip, softer grip areas and high working speeds due to the hard grip areas, which allow a quick hand switch.

Compact shape



With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Web link

https://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_stubby_esd_1.html

Wera - Kraftform Kompakt Stubby ESD 1
05057472001 - 4013288214584

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt Stubby ESD 1, 10 pieces

ESD Series



Set contents:

811/1 ESD Stubby Bitholding screwdriver, magnetic, 1/4" x 54 mm



05008881001 1x 1/4" x 54 mm



851/1 Z bits, PH 0 x 25 mm



05056500001 1x PH 0 x 25 mm
05072070001 1x PH 1 x 25 mm
05072072001 1x PH 2 x 25 mm



851/1 J bits, PH 00 x 25 x 2 mm



05135040001¹⁾ 1x PH 00 x 25 x 2 mm
1) Size 00 modified according to JCIS 00 (Japanese Camera Industrial Standard)



800/1 Z bits, 0.5 x 3 x 25 mm



05056200001 1x 0.5 x 3 x 25 mm
05072055001 1x 0.6 x 4.5 x 25 mm
05072059001 1x 1 x 5.5 x 25 mm
05072061001 1x 1.2 x 6.5 x 25 mm
05072063001 1x 1.2 x 8 x 25 mm



Web link

https://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_stubby_esd_1.html

Wera - Kraftform Kompakt Stubby ESD 1
05057472001 - 4013288214584

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de