

Kraftform Kompakt 60 KK, 17 pieces

Kraftform Kompakt 60, 62



EAN:	4013288165503	Size:	155x130x55 mm
Part number:	05059294001	Weight:	476 g
Article number:	KK 60 KK	Country of origin:	CZ
		Customs tariff number:	82079030

- Pouch with 89 mm-long bits
- Kraftform holder with Rapidaptor quick-release chuck
- Rapidaptor quick-release chuck allows rapid bit change
- Tough viscous bits for universal use
- Ballpoint bits allow a swivelling of the tool axis

Pouch with 89-mm long ballpoint bits, which enable a swivelling or pivoting of the tool axis. Includes 816 R Kraftform holder with Rapidaptor quick-release chuck and multi-component Kraftform handle for low-fatigue working. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Suitable for manual and power tool operations; 17-piece.



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_kk.html

Wera - KK 60 KK
05059294001 - 4013288165503

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

For fixed workplace locations and external sites



Why is the right tool so often not at hand? The reason: too many tools and overly-heavy tool bags can make it bothersome to carry them onsite. So for us it was a clear challenge: to design a tool that is suitable for a whole host of applications and can be easily taken along to jobs at other sites. Our solution: Kraftform Kompakt tools. A handle into which blades with a range of different profiles can be inserted. Compactly and protectively housed in a light and robust textile pouch or plastic box.




Frequently, users have to work with their tools at a fixed workplace location as well as at external sites. Just as frequently, it is only on site that a decision is taken as to whether to work manually or with a power tool. The Kraftform Kompakt tool sets equip the user for both types of operation with just single set. Additionally, the sets are kept in belt pouches or plastic cases. This keeps them secure and clean and means that they are clearly arranged for easy tool selection, something that is very practical when they are to be used or transported.

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Manual and power tool operations



The sets come with a Kraftform handle, quick-release chuck and bits for manual and power tool operations.

Ball tip



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

Chuck-all




The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_kk.html

Wera - KK 60 KK
05059294001 - 4013288165503

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Kraftform Kompakt 60 KK, 17 pieces

Kraftform Kompakt 60, 62

Set contents:

816 R Bitholding screwdriver with Rapidaptor quick-release chuck, 1/4" x 119 mm



05051462001 1x 1/4" x 119 mm



851/4 Z bits, PH 1 x 89 mm



05059760001 1x PH 1 x 89 mm

05059775001 1x PH 2 x 89 mm

05059795001¹⁾ 1x PH 3 x 89 mm

1) Hexagonal blade

855/4 Z bits, PZ 1 x 89 mm



05060029001 1x PZ 1 x 89 mm

05060035001 1x PZ 2 x 89 mm

05060043001¹⁾ 1x PZ 3 x 89 mm

1) Hexagonal blade

867/4 KK TORX® bits, TX 10 x 89 mm



05059700001 1x TX 10 x 89 mm

05059701001 1x TX 15 x 89 mm

05059702001 1x TX 20 x 89 mm

05059703001 1x TX 25 x 89 mm

05059704001 1x TX 30 x 89 mm

05059705001¹⁾ 1x TX 40 x 89 mm

1) Hexagonal blade

842/4 Bits, 3 x 89 mm



05059680001 1x 3 x 89 mm

05059681001 1x 4 x 89 mm

05059682001 1x 5 x 89 mm

05059683001 1x 6 x 89 mm

Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_kk.html

Wera - KK 60 KK
05059294001 - 4013288165503

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de