Kraftform Kompakt 60, 62


















 Part number:
 05059295001
 Weight:
 554 g

 Article number:
 KK 60
 Country of origin:
 CZ

Customs tariff 82079030

number:



- Multi-component Kraftform handle of the bit holder for fast and ergonomic screwdriving
- · Hexagonal anti-roll feature against rolling away
- Hex-Plus allows socket head screws to live longer
- Suitable for docking with the Wera 2go system.

Folding bag with 89 mm long bits. Including Kraftform 816 R bitholding screwdriver with Rapidaptor quick-release chuck and multi-component Kraftform handle for fatigue-free working. Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. Suitable for manual and machine operated couplings. 17-piece set.











Why is the right tool so often not at

hand? The reason: too many tools

and overly-heavy tool bags can

make it bothersome to carry them

onsite. So for us it was a clear

challenge: to design a tool that is

suitable for a whole host of

applications and can be easily

taken along to jobs at other sites.

Our solution: Kraftform Kompakt

tools. A handle into which blades

with a range of different profiles

can be inserted. Compactly and protectively housed in a light and

robust textile pouch or plastic box.

Kraftform Kompakt 60, 62



For fixed workplace locations and external sites



Frequently, users have to work with their tools at a fixed workplace location as well as at external sites. Just as frequently, it is only on site that a decision is taken as to whether to work manually or with a power tool. The Kraftform Kompakt tool sets equip the user for both types of operation with just single set. Additionally, the sets are kept in belt pouches or plastic cases. This keeps them secure and clean and means that they are clearly arranged for easy tool selection, something that is very practical when they are to be used or transported.

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Chuck-all



The Rapidaptor quick-release chucks hold ¼" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Web link https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60.html

Kraftform Kompakt 60, 62



Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Kraftform Kompakt 60, 17 pieces

Kraftform Kompakt 60, 62




Set contents:

816 R Bitholding screwdriver with Rapidaptor quick-release chuck, 1/4" x 119 mm

© 05051462001 1x 1/4" x 119 mm



851/4 Z bits, PH 1 x 89 mm



855/4 Z bits, PZ 1 x 89 mm

(1)	05060029001	1x	PZ 1 x 89 mm
The E	05060035001	1x	PZ 2 x 89 mm
	05060043001 ¹⁾	1x	PZ 3 x 89 mm
	Hexagonal blade		

867/4 Z TORX® BO bits with bore hole, TX 10 x 89 mm

\odot	05060050001	1x	TX 10 x 89 mm
	05060051001	1x	TX 15 x 89 mm
Weed Weed	05060052001	1x	TX 20 x 89 mm
	05060053001	1x	TX 25 x 89 mm
	05060054001	1x	TX 30 x 89 mm

800/4 Z bits, 1 x 5.5 x 89 mm

•	05059488001	1x	1 x 5.5 x 89 mm
In In			
040/4 7 hito 2 v 00 mm			

840/4 Z bits, 3 x 89 mm

0	05059630001	1x	3 x 89 mm
M Weec	05059631001	1x	4 x 89 mm
	05059632001	1x	5 x 89 mm
	050596330011)	1x	6 x 89 mm
	1) Hexagonal blade		

Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm

Web link

 $https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60.html$